



SA4J Type 4 safety light curtain

SA4J Type 4 safety light curtain selection table

Dimensions



Selection rules



Optical axis spacing	10mm			20mm			30mm			40mm		
	Mode	Protection height (mm)	total height (mm)	Mode	Protection height (mm)	total height (mm)	Mode	Protection height (mm)	total height (mm)	Mode	Protection height (mm)	total height (mm)
8				SA4J-0820	140	166	SA4J-0830	210	246	SA4J-0840	280	326
10				SA4J-1020	180	206	SA4J-1030	270	306	SA4J-1040	360	406
12				SA4J-1220	220	246	SA4J-1230	330	366	SA4J-1240	440	486
14				SA4J-1420	260	286	SA4J-1430	390	426	SA4J-1440	520	566
16	SA4J-1610	150	166	SA4J-1620	300	326	SA4J-1630	450	486	SA4J-1640	600	646
18	SA4J-1810	170	186	SA4J-1820	340	366	SA4J-1830	510	546	SA4J-1840	680	726
20	SA4J-2010	190	206	SA4J-2020	380	406	SA4J-2030	570	606	SA4J-2040	760	806
22	SA4J-2210	210	226	SA4J-2220	420	446	SA4J-2230	630	666	SA4J-2240	840	886
24	SA4J-2410	230	246	SA4J-2420	460	486	SA4J-2430	690	726	SA4J-2440	920	966
26	SA4J-2610	250	266	SA4J-2620	500	526	SA4J-2630	750	786	SA4J-2640	1000	1046
28	SA4J-2810	270	286	SA4J-2820	540	566	SA4J-2830	810	846	SA4J-2840	1080	1126
30	SA4J-3010	290	306	SA4J-3020	580	606	SA4J-3030	870	906	SA4J-3040	1160	1206
32	SA4J-3210	310	326	SA4J-3220	620	646	SA4J-3230	930	966	SA4J-3240	1240	1286
34	SA4J-3410	330	346	SA4J-3420	660	686	SA4J-3430	990	1026	SA4J-3440	1320	1366
36	SA4J-3610	350	366	SA4J-3620	700	726	SA4J-3630	1050	1086	SA4J-3640	1400	1446
38	SA4J-3810	370	386	SA4J-3820	740	766	SA4J-3830	1110	1146	SA4J-3840	1480	1526
40	SA4J-4010	390	406	SA4J-4020	780	806	SA4J-4030	1170	1206	SA4J-4040	1560	1606
42	SA4J-4210	410	426	SA4J-4220	820	846	SA4J-4230	1230	1266	SA4J-4240	1640	1686
44	SA4J-4410	430	446	SA4J-4420	860	886	SA4J-4430	1290	1326	SA4J-4440	1720	1766
46	SA4J-4610	450	466	SA4J-4620	900	926	SA4J-4630	1350	1386	SA4J-4640	1800	1846
48	SA4J-4810	470	486	SA4J-4820	940	966	SA4J-4830	1410	1446	SA4J-4840	1880	1926
50	SA4J-5010	490	506	SA4J-5020	980	1006	SA4J-5030	1470	1506	SA4J-5040	1960	2006
52	SA4J-5210	510	526	SA4J-5220	1020	1046	SA4J-5230	1530	1566	SA4J-5240	2040	2086
54	SA4J-5410	530	546	SA4J-5420	1060	1086	SA4J-5430	1590	1626	SA4J-5440	2120	2166
56	SA4J-5610	550	566	SA4J-5620	1100	1126	SA4J-5630	1650	1686	SA4J-5640	2200	2246
58	SA4J-5810	570	586	SA4J-5820	1140	1166	SA4J-5830	1710	1746	SA4J-5840	2280	2326
60	SA4J-6010	590	606	SA4J-6020	1180	1206	SA4J-6030	1770	1806	SA4J-6040	2360	2406
62	SA4J-6210	610	626	SA4J-6220	1220	1246	SA4J-6230	1830	1866	SA4J-6240	2440	2486
64	SA4J-6410	630	646	SA4J-6420	1260	1286	SA4J-6430	1890	1926	SA4J-6440	2520	2566
66	SA4J-6610	650	666	SA4J-6620	1300	1326	SA4J-6630	1950	1986	SA4J-6640	2600	2646
68	SA4J-6810	670	686	SA4J-6820	1340	1366	SA4J-6830	2010	2046	SA4J-6840	2680	2726
70	SA4J-7010	690	706	SA4J-7020	1380	1406	SA4J-7030	2070	2106	SA4J-7040	2760	2806
72	SA4J-7210	710	726	SA4J-7220	1420	1446	SA4J-7230	2130	2166	SA4J-7240	2840	2886
74	SA4J-7410	730	746	SA4J-7420	1460	1486	SA4J-7430	2190	2226	SA4J-7440	2920	2966
76	SA4J-7610	750	766	SA4J-7620	1500	1526	SA4J-7630	2250	2286			
78	SA4J-7810	770	786	SA4J-7820	1540	1566	SA4J-7830	2310	2346			
80	SA4J-8010	790	806	SA4J-8020	1580	1606	SA4J-8030	2370	2406			
82	SA4J-8210	810	826	SA4J-8220	1620	1646	SA4J-8230	2430	2466			
84	SA4J-8410	830	846	SA4J-8420	1660	1686	SA4J-8430	2490	2526			
86	SA4J-8610	850	866	SA4J-8620	1700	1726	SA4J-8630	2550	2586			
88	SA4J-8810	870	886	SA4J-8820	1740	1766	SA4J-8830	2610	2646			
90	SA4J-9010	890	906	SA4J-9020	1780	1806	SA4J-9030	2670	2706			
92	SA4J-9210	910	926	SA4J-9220	1820	1846	SA4J-9230	2730	2766			
94	SA4J-9410	930	946	SA4J-9420	1860	1886	SA4J-9430	2790	2826			
96	SA4J-9610	950	966	SA4J-9620	1900	1926	SA4J-9630	2850	2886			
98	SA4J-9810	970	986	SA4J-9820	1940	1966	SA4J-9830	2910	2946			

Note: The optical axis spacing of this type of product includes 10mm, 20mm, 30mm, 40mm, which is not fully reflected in the selection table. If your choice is not included, please contact us for your selection. The total height of all products in this series = (optical axis spacing * number of optical axes) + 6mm.